

ITEC[®]
FRONTMATEC
By Fortifi

Cleaning basin type 20550 Outstanding in design and operation

HYGIENE




Photo 1



Photo 2



≡ In line with demand, energy and cost-saving, but also more hygienic are the new contactless fittings.

≡ Here, water only flows when the hands are put under the faucet, therefore only during the actual cleaning process of the hands.

≡ For this reason and by the use of a water-saving spray head the water consumption can be reduced to 1-1,5 litres.

≡ The time water keeps on running after a cleaning process is limited to 1 second.

≡ This ensures a minimum of switching operations and therefore an extended life of the technical equipment.

≡ In case of damage or wilful opening of the sensor the water stops running after 30 sec. at the latest.



≡ Photo 15: centralised drain




≡ Photo 10: Cleaning trough type 20555-3W



≡ Photo 11: Type 20555



≡ Photo 12: Type 20550



≡ Photo 13: Double cleaning trough type 20550-5SD

Model:

- ≡ Cleaning basins and cleaning troughs type 20550 for wall, platform or floor fixing.
- ≡ Easy installation
- ≡ Drawn basin with back panel completely made of stainless steel, material no. 1.4301, surfaces finish - ground.
- ≡ Contactless operation of fittings is achieved by an electronic system placed in the faucet working with 24 V low voltage.
- ≡ Control system protection class IP 65. Primary and

secondary fuse on the board. Board fully sealed.

- ≡ By avoiding contamination and by lowest water- and energy consumption the function system guarantees maximum hygiene at the lowest cost.
- ≡ The cleaning basin type 20550 W corresponds to the EU- and US-hygiene requirements as well as to the VDE-guidelines, section electric prescriptions.
- ≡ Easy cleaning by large-scale measurements.

