

ITEC[®]
FRONTMATEC
 By Fortifi



Photo 4



Photo 5

A clear rinsing is done by rinsing the brushes with tap water after the operation with cleaning detergent and disinfectant.

The open geometric shape of the casing and the brushes' position guarantee an optimal hygiene of the appliance. Equipped with the P3 click-in-system bin the machine ensures a safe handling of the cleaning detergent and disinfectant.

Due to its small measurements the appliance is perfect for a placement in small passages and niches.

All elements in danger of corrosion have been made of stainless steel or resistant plastics.

Technical data Type 23840

Approx. measurements outside:	height x width x depth	1125 x 1222 x 515 mm
Connection to the network:		400 V, 3/ N/ PE
Network frequency:		50 - 60 Hz
Rated power:		0.25 kW
Water supply:	Mixed Water R3/ 4",	T _{max} = 43° C
Drain:		DN 50/ R 1 1/ 2"
Protective device:		IP65

Technical changes subject to alterations.

