

## HYGOMAT COMFORT

4 times faster than manually putting on

- no electrical power needed
- easy to use, no need for bending over
- easy and quick handling
- with handrail for extra comfort
- capacity up to 220 overshoes
- with window for easy control of rest capacity
- refilled with overshoes within seconds
- weight: 21 kg



### HYGOMAT COMFORT

**HYGO STAR**

Art. No.	size	colour	PU/ piece
88811	74 x 30 x 73cm	white/ grey	1



Product video on  
[www.franz-mensch.de](http://www.franz-mensch.de)

## HYGOMAT CLEANROOM

- description as above, additionally:
- extraordinary hygienic, made of stainless steel (backside and sides)
- easy to clean and disinfect
- with 2 castors on the backside – can be relocated, very flexible
- especially for clean rooms and pharmaceutical companies
- extremely clean, because overshoe is not contaminated due to hand contact
- 100% hygienic, no cross contaminations
- weight: 20 kg

### HYGOMAT CLEANROOM

**HYGO STAR**

Art. No.	size	colour	PU/ piece
88813	74 x 30 x 73cm	grey	1



## HYGOMAT CLASSIC

- saves space, no power needed
- capacity up to 110 overshoes
- easy handling, quiet
- hands free function
- weight: ca. 8,5 kg



### HYGOMAT CLASSIC

**HYGO STAR**

Art. No.	size	colour	PU/ piece
88810	70 x 32 x 28 cm	white/ grey	1


\*certified for cleanroom use ISO class 5\* according to EN ISO 14644-1 \* = max. 100 particles of a max. diameter of 0,5 µm per cubic feet (3,5 particles per litres)

### For product, plant and stuff hygiene

This new released overshoe dispenser HYGOMAT is especially made for staff members and visitors of hospitals, companies, schools, hotels, food service industry, dairies, building industry, show rooms, model houses, laboratories, production plants, offices, protections areas and clean rooms. Easy to handle – the portable Hygomat overshoe dispenser can be set up everywhere and is suitable for every kind of shoe. No more need to bend down or try on. No more waiting periods.

#### Easy use:

The user puts his foot on the overshoe in the machine (see figure 1). He pulls out the foot backwards. Now the overshoe fits perfectly (see figure 4). **Only for use with original HYGOMAT overshoes.**



DESCUBRE MÁS EN

[www.taglermaq.cl](http://www.taglermaq.cl)

### Overshoe CPE

- strong quality, 60 my
- **waterproof**



Overshoe CPE for HYGOMAT

**HYGOSTAR**

Art. No.	size	colour	PU/ piece
2850H	47 cm	blue	10 x 110

### Overshoe with strong CPE sole

- nonwoven at the top, permeable to air
- at the bottom strong CPE sole
- very strong, tearproof
- waterproof sole



Overshoe with strong CPE sole for HYGOMAT

**HYGOSTAR**

Art. No.	size	colour	PU/ piece
2860H	44 cm	white/ blue	10 x 70

### Nonwoven overshoe with CPE coating

- waterproof sole
- inside nonwoven
- outside CPE coated
- particularly for smooth surfaces
- **very slip resistant**



Nonwoven overshoe with CPE coating for HYGOMAT

**HYGOSTAR**

Art.No.	size	colour	PU/ piece
28504H	44cm	white	10 x 80

### PP overshoe with structured sole

- permeable to air
- at the bottom with anti-slip structure made of CPE
- for dry areas



PP overshoe with structured sole for HYGOMAT

**HYGOSTAR**

Art.No.	size	colour	PU/ piece
28606H	46 cm	light blue	10 x 100

### PP overshoe with antistatic band

- PP nonwoven
- permeable to air
- antistatic duet to deducible black contact band
- note: band has to be in contact with the skin in order to ground the body



PP overshoe with antistatic band for HYGOMAT

**HYGOSTAR**

Art.No.	size	colour	PU/ piece
28602H	46 cm	blue	10 x 100

### Overshoe ECONOMY

- PE, waterproof
- one size
- ideal as protection from dirt, only for indoor areas and short time use



Overshoe ECONOMY for HYGOMAT

**HYGOSTAR**

Art.No.	size	colour	PU/ piece
28509H	46 cm	blue	20 x 110